


Technology pivot:
Bottom and Back Panel Measurement
16MM Density Panel




- 1 Bottom panel width=Inside Cabinet Width-75±0.5
- 2 Bottom panel length=Runner length-10MM
- Back panel height= 183MM
- Back panel width=Inside Cabinet Width-87±0.5

Special Features:

- Length:270,300,350,400,450,500,550mm.
- The drawer side-board is 203mm high.
- Drawer width can be designed freely with automatic error adjustment.
- Hidden full pulout silencing sliding slid can bear 40kg and enjoys
- excellent stability and quite and smooth sliding performance.
- Quick installation and dismantle.
- Newly-designed built-in damper is free from reinstallation and ensures soft and smooth drawer movements.


Basic length	Internally usable drawer depth	Minimum installation depth of drawer	Minimum installation height
300mm	274mm	300mm	225mm
350mm	324mm	350mm	225mm
400mm	374mm	400mm	225mm
450mm	424mm	450mm	225mm
500mm	474mm	500mm	225mm
550mm	524mm	550mm	225mm

1. Guide



Left/Right Length : 300mm
350mm
400mm
450mm
500mm
550mm

2.Drawer Side & Decorative Cap



Left/Right Length:
300mm
350mm
400mm
450mm
500mm
550mm

3.Back connector



Left / Right

4.Front connector




Left / Right

5.Upper pin




Runner Installation(mm)




Basic length:300/350/400/450/500/550


Inside Cabinet Dimension




Front Panel Mounting Positions




Front Fixing Brackets Positions




Back Panel Mounting Positions



Front fixing brackets mounting




B Side overlay(user-defined)



- 1 Tighten the fixing screw after installed the panel
- 2 Press the upper pin into panel after installed the panel

A B Side overlay(user-defined)




- 1 Take out the back cover
- 2 Take out the upper pin


Front panel height adjustment : ±2mm







Front panel side adjustment : right/leftmm







Front panel side adjustment : left/rightmm






Mounting the drawer




Installing the drawer



Function of the damper



Removing the drawer



Push the metal spring part from the panel & pull out.